

EA966CC-21～-36 (ステンレス製スリットカラー)



★ 特長

- シャフトに傷をつける事なく固定ができます。
- スライドシャフトや頻繁に取付け位置を変更する所に最適です。

■ 材質 … ステンレス(SUS304)

品番	内径 φ B H8	外径 φ D±0.1	幅 L±0.1	W	X	Y	A	トメジ M	六角穴付 ボルト
EA966CC-21	5	20	10	1	6	4	6	M4XP0.7	M4X10
EA966CC-22	6	20	10	1	6	4	6	M4XP0.7	M4X10
EA966CC-23	8	25	10	1.5	8	5	9	M4XP0.7	M4X12
EA966CC-24	10	30	10	1.5	9	5	11	M4XP0.7	M4X12
EA966CC-25	12	30	10	1.5	10	5	11	M4XP0.7	M4X12
EA966CC-26	13	30	10	1.5	10	5	11	M4XP0.7	M4X12
EA966CC-27	15	35	12	1.5	12	6	13	M5XP0.8	M5X16
EA966CC-28	16	35	12	1.5	12	6	13	M5XP0.8	M5X16
EA966CC-29	20	40	12	1.5	14	7	15	M5XP0.8	M5X16
EA966CC-30	25	45	12	1.5	17	7	18	M5XP0.8	M5X16
EA966CC-31	25	50	15	1.5	18	10	18	M6XP1.0	M6X25
EA966CC-32	30	55	15	1.5	18	10	—	M6XP1.0	M6X25
EA966CC-33	35	60	15	2	23	12	—	M6XP1.0	M6X25
EA966CC-34	40	70	18	2	26	13	—	M8XP1.25	M8X30
EA966CC-35	45	75	18	3	28	14	—	M8XP1.25	M8X30
EA966CC-36	50	85	22	3	32	16	—	M10XP1.5	M10X35

(単位 mm)

