

EA966CE-21～-36

(ステンレス製セパレートカラー)



★ 特長

- 機械組立後の脱着が可能なセパレートタイプのカラーです。
- 後付けや分解困難なシャフト部分に最適です。
- 錆の心配がなく、食品機械や半導体装置に最適です。

■ 材質 … ステンレス(SUS304)

品番	内径 φ B H8	外径 φ D±0.1	幅 L±0.1	W	X	Y	トメジ M	六角穴付 ボルト
EA966CE-21	5	20	10	1	6	4	M4XP0.7	M4X10
EA966CE-22	6	20	10	1	6	4	M4XP0.7	M4X10
EA966CE-23	8	25	10	1.5	8	5	M4XP0.7	M4X12
EA966CE-24	10	30	10	1.5	9	5	M4XP0.7	M4X12
EA966CE-25	12	30	10	1.5	10	5	M4XP0.7	M4X12
EA966CE-26	13	30	10	1.5	10	5	M4XP0.7	M4X12
EA966CE-27	15	35	12	1.5	12	6	M5XP0.8	M5X16
EA966CE-28	16	35	12	1.5	12	6	M5XP0.8	M5X16
EA966CE-29	20	40	12	1.5	14	7	M4XP0.7	M4X16
EA966CE-30	25	45	12	1.5	17	7	M5XP0.8	M5X16
EA966CE-31	25	50	15	1.5	18	10	M6XP1.0	M6X25
EA966CE-32	30	55	15	1.5	20	10	M6XP1.0	M6X25
EA966CE-33	35	60	15	2	23	12	M6XP1.0	M6X25
EA966CE-34	40	70	18	2	26	13	M8XP1.75	M8X30
EA966CE-35	45	75	18	3	28	14	M8XP1.75	M8X30
EA966CE-36	50	85	22	3	32	16	M10XP1.5	M10X35

(単位 mm)

