

呼び番号 RodendNo.	主要寸法 (mm) Main dimensions											許容 傾斜各		限界荷重 (kgf) LoadLimit		重量 Weight (g)
	B	W	G	O	D	F	H	A	E	M	P	α2	ラジアル Radial 荷重 Load	アキシアル Axial 荷重 Load		
	EA966DG-5A,DH-5A	DM5	5	8	6	7.71	16	33	41	20	11.11	M5×0.8	3	12	590	
EA966DG-6A,DH-6A	DM6	6	9	6.7	8.96	18	36	45	22	12.7	M6×1	3.3	11	650	250	19
EA966DG-8A,DH-8A	DM8	8	12	9	10.4	22	42	53	25	15.88	M8×1.25	4.5	12	800	300	36
EA966DG-10A,DH-10A	DM10	10	14	11	12.92	26	48	61	29	19.05	M10×1.5	5.5	12	1,050	390	60
EA966DG-12A,DH-12A	DM12	12	16	12	15.43	30	54	69	33	22.23	M12×1.75	6	13	1,300	500	89
EA966DG-14A,DH-14A	DM14	14	19	14	16.86	34	60	77	36	25.4	M14×2	7	14	1,700	650	129
EA966DG-16A,DH-16A	DM16	16	21	15	19.39	38	66	85	40	28.58	M16×2	7.5	14	2,100	800	181
EA966DG-18A,DH-18A	DM18	18	23	17	21.89	42	72	93	44	31.75	M18×1.5	8.5	14	2,550	950	250
EA966DG-20A,DH-20A	DM20	20	25	18	24.38	46	78	101	47	34.93	M20×1.5	9	14	3,000	1,100	333
	DM22	22	28	20	25.84	50	84	109	51	38.1	M22×1.5	10	15	3,550	1,350	430
	DM25	25	31	22	29.6	56	94	122	57	42.86	M24×2	11	15	4,500	2,830	575
	DM30	30	37	26	34.8	67	110	143.5	66	50.8	M30×2	13	15	7,000	3,960	996

