

RATCHET ASSEMBLY W/ CLIPS

304 AND 316 STAINLESS STEEL & WEBBING



EA982BB-31 ~ -43

ITEM	WEBBING (width)	LENGTH (overall)	LENGTH (fixed end)	CLIPS (part #)	WLL (lb)	WT (lb)
BLACK						
S0201-0325	1"	3'	12"	S0172-0080	440	0.86
S0201-0425	1"	4'	12"	S0172-0080	440	0.89
S0201-0525 (-31)	1"	5'	12"	S0172-0080	440	0.92
S0201-0625	1"	6'	12"	S0172-0080	440	0.95
S0201-0825	1"	8'	12"	S0172-0080	440	1.00
S0201-1025 (-32)	1"	10'	12"	S0172-0080	440	1.05
S0201-1225	1"	12'	12"	S0172-0080	440	1.11
S0201-1625	1"	16'	12"	S0172-0080	440	1.23
S0201-2025 (-33)	1"	20'	12"	S0172-0080	440	1.35
S0201-2525	1"	25'	12"	S0172-0080	440	1.50
BLUE						
S0201-0325-B	1"	3'	12"	S0172-0080	440	0.86
S0201-0425-B	1"	4'	12"	S0172-0080	440	0.89
S0201-0525-B	1"	5'	12"	S0172-0080	440	0.92
S0201-0625-B	1"	6'	12"	S0172-0080	440	0.95
S0201-0825-B	1"	8'	12"	S0172-0080	440	1.00
S0201-1025-B	1"	10'	12"	S0172-0080	440	1.05
S0201-1225-B	1"	12'	12"	S0172-0080	440	1.11
S0201-1625-B	1"	16'	12"	S0172-0080	440	1.23
S0201-2025-B	1"	20'	12"	S0172-0080	440	1.35
WHITE						
S0201-0525-W	1"	5'	12"	S0172-0080	440	0.92
S0201-1025-W	1"	10'	12"	S0172-0080	440	1.05
S0201-2025-W	1"	20'	12"	S0172-0080	440	1.35
BLACK						
S0203-0338	1-1/2"	3'	14"	S0172-0100	1,100	2.38
S0203-0438	1-1/2"	4'	14"	S0172-0100	1,100	2.42
S0203-0538 (-41)	1-1/2"	5'	14"	S0172-0100	1,100	2.46
S0203-0638	1-1/2"	6'	14"	S0172-0100	1,100	2.50
S0203-0838	1-1/2"	8'	14"	S0172-0100	1,100	2.58
S0203-1038 (-42)	1-1/2"	10'	14"	S0172-0100	1,100	2.66
S0203-1238	1-1/2"	12'	14"	S0172-0100	1,100	2.74
S0203-1638	1-1/2"	16'	14"	S0172-0100	1,100	2.90
S0203-2038 (-43)	1-1/2"	20'	14"	S0172-0100	1,100	3.06
BLUE						
S0203-0338-B	1-1/2"	3'	14"	S0172-0100	1,100	2.38
S0203-0438-B	1-1/2"	4'	14"	S0172-0100	1,100	2.42
S0203-0538-B	1-1/2"	5'	14"	S0172-0100	1,100	2.46
S0203-0638-B	1-1/2"	6'	14"	S0172-0100	1,100	2.50
S0203-0838-B	1-1/2"	8'	14"	S0172-0100	1,100	2.58
S0203-1038-B	1-1/2"	10'	14"	S0172-0100	1,100	2.66
S0203-1238-B	1-1/2"	12'	14"	S0172-0100	1,100	2.74
S0203-1638-B	1-1/2"	16'	14"	S0172-0100	1,100	2.90
S0203-2038-B	1-1/2"	20'	14"	S0172-0100	1,100	3.06
BLACK						
S0204-0350	2"	3'	17"	S0172-0120	1,650	3.72
S0204-0450	2"	4'	17"	S0172-0120	1,650	3.78
S0204-0550	2"	5'	17"	S0172-0120	1,650	3.84
S0204-0650	2"	6'	17"	S0172-0120	1,650	3.90
S0204-0850	2"	8'	17"	S0172-0120	1,650	4.02
S0204-1050	2"	10'	17"	S0172-0120	1,650	4.13
S0204-1250	2"	12'	17"	S0172-0120	1,650	4.25
S0204-1650	2"	16'	17"	S0172-0120	1,650	4.49
S0204-2050	2"	20'	17"	S0172-0120	1,650	4.73
BLUE						
S0204-0350-B	2"	3'	17"	S0172-0120	1,650	3.72
S0204-0450-B	2"	4'	17"	S0172-0120	1,650	3.78
S0204-0550-B	2"	5'	17"	S0172-0120	1,650	3.84
S0204-0650-B	2"	6'	17"	S0172-0120	1,650	3.90
S0204-0850-B	2"	8'	17"	S0172-0120	1,650	4.02
S0204-1050-B	2"	10'	17"	S0172-0120	1,650	4.13
S0204-1250-B	2"	12'	17"	S0172-0120	1,650	4.25
S0204-1650-B	2"	16'	17"	S0172-0120	1,650	4.49
S0204-2050-B	2"	20'	17"	S0172-0120	1,650	4.73

NOTE: INFORMATION ON RATCHET BUCKLES CAN BE FOUND ON PAGE 104. FOR INFORMATION ON HARNESS CLIPS SEE PAGE 60.

