

Product Data Sheet



BPA-VPA 50K-EL

EAN 4047526328054
ID 328054

Light duty fixed castor with top plate fitting, Wheel with solid rubber tyres, with synthetic rim, electrically conductive

Bracket:
Made of pressed steel. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

Wheels:
Made of high-quality solid rubber, very high operational comfort, low-noise operation, ve good floor preservation.

Tread/tyre: Made of high-quality solid rubber.

Tread colours black

Wheel centre/rim:
Made of high-quality, impact-resistant nylon. Pressed-on tyre.

Wheel centre colour: black

Variant: electrically conductive



Rolling resistance
■ ■ ■ ■ □ Very good

Operating noise
■ ■ □ □ □ Satisfactory

Floor surface preservation
■ ■ ■ ■ □ Very good

Product Data Sheet



Technical data

Plate size		60 x 60
Bolt hole spacing		38x38/48x48
Bolt hole Ø		6,2
Wheel Ø		50 mm (D)
Wheel width		18 mm (T2)
Load capacity		30 kg
Total height		71 mm (H)
unit weight		0,2 kg
Temperature resistance		-20 ° C
Temperature resistance to		60 ° C
tread and tyre hardness		80° Shore A
Bearing type		Ball bearing

