

Product Data Sheet



BPA-VPA 75K-EL

EAN 4047526276706

ID 276709

Light duty fixed castor with top plate fitting, Wheel with solid rubber tyres, with synthetic rim, electrically conductive

Bracket:

Made of pressed steel. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

Wheels:

Made of high-quality solid rubber, very high operational comfort, low-noise operation, very good floor preservation.

Tread/tyre: Made of high-quality solid rubber.

Tread colours black

Wheel centre/rim:

Made of high-quality, impact-resistant nylon. Pressed-on tyre.

Wheel centre colour: black

Variant: electrically conductive



Rolling resistance

■ ■ ■ ■ □ Very good

Operating noise

■ ■ □ □ □ Satisfactory

Floor surface preservation

■ ■ ■ ■ □ Very good

Product Data Sheet



Technical data

Plate size		60 x 60
Bolt hole spacing		38x38/48x48
Bolt hole Ø		6,2
Wheel Ø		75 mm (D)
Wheel width		25 mm (T2)
Load capacity		45 kg
Total height		100 mm (H)
unit weight		0,3 kg
Temperature resistance		-20 ° C
Temperature resistance to		60 ° C
tread and tyre hardness		80° Shore A
Bearing type		Ball bearing

