

Product Data Sheet



LKPA-VPA 125K-FI-EL

EAN 4047526303341

ID 303347

Light duty swivel castor with top plate fitting with 'stop-fix' brake, Wheel with solid rubber tyres, with synthetic rim, electrically conductive

Bracket:

Made of pressed steel, with double ball bearing in the swivel head, strong central kingpin, ball protection by the special top plate and ball disc design. The special Blickle dynamic riveting process of the swivel head results in minimal swivel head play and smooth rolling characteristics with an increased service life achieved by the work hardening of the ball race grooves. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

Wheels:

Made of high-quality solid rubber, very high operational comfort, low-noise operation, very good floor preservation.

Tread/tyre: Made of high-quality solid rubber.

Tread colours black

Wheel centre/rim:

Made of high-quality, impact-resistant nylon. Pressed-on tyre.

Wheel centre colour: black

Variant: electrically conductive



Rolling resistance

■ ■ ■ ■ □ Very good

Operating noise

■ ■ □ □ □ Satisfactory













Floor surface preservation

■ ■ ■ ■ □ Very good

Product Data Sheet



Technical data

Plate size		90 x 66
Bolt hole spacing		75x45/61x51
Bolt hole Ø		8,5
Wheel Ø		125 mm (D)
Wheel width		25 mm (T2)
Load capacity		75 kg
Total height		161 mm (H)
Offset swivel castor		40 mm
unit weight		0,9 kg
Temperature resistance		-20 ° C
Temperature resistance to		60 ° C
tread and tyre hardness		80° Shore A
Bearing type		Ball bearing

