

# Product Data Sheet



## BKPA-VPA 101K-EL

EAN 4047526376000  
ID 376004

Light duty fixed castor with top plate fitting, Wheel with solid rubber tyres, with synthetic rim, electrically conductive

**Bracket:**  
Made of pressed steel. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

**Wheels:**  
Made of high-quality solid rubber, very high operational comfort, low-noise operation, very good floor preservation.

**Tread/tyre:** Made of high-quality solid rubber.

**Tread colours** black

**Wheel centre/rim:**  
Made of high-quality, impact-resistant nylon. Pressed-on tyre.

**Wheel centre colour:** black

**Variant:** electrically conductive



**Rolling resistance**  
■ ■ ■ ■ □ Very good












**Operating noise**  
■ ■ □ □ □ Satisfactory

**Floor surface preservation**  
■ ■ ■ ■ □ Very good

# Product Data Sheet



## Technical data

Plate size		90 x 66
Bolt hole spacing		75x45/61x51
Bolt hole Ø		8,5
Wheel Ø		100 mm (D)
Wheel width		32 mm (T2)
Load capacity		80 kg
Total height		136 mm (H)
unit weight		0,6 kg
Temperature resistance		-20 ° C
Temperature resistance to		60 ° C
tread and tyre hardness		80° Shore A
Bearing type		Ball bearing

