

Product Data Sheet



BKPA-VPA 125K-EL

EAN 4047526349097

ID 349092

Light duty fixed castor with top plate fitting, Wheel with solid rubber tyres, with synthetic rim, electrically conductive

Bracket:

Made of pressed steel. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

Wheels:

Made of high-quality solid rubber, very high operational comfort, low-noise operation, very good floor preservation.

Tread/tyre: Made of high-quality solid rubber.

Tread colours black

Wheel centre/rim:

Made of high-quality, impact-resistant nylon. Pressed-on tyre.

Wheel centre colour: black

Variant: electrically conductive



Rolling resistance

■ ■ ■ ■ □ Very good

Operating noise

■ ■ □ □ □ Satisfactory












Floor surface preservation

■ ■ ■ ■ □ Very good

Product Data Sheet



Technical data

Plate size		90 x 66
Bolt hole spacing		75x45/61x51
Bolt hole Ø		8,5
Wheel Ø		125 mm (D)
Wheel width		25 mm (T2)
Load capacity		75 kg
Total height		161 mm (H)
unit weight		0,6 kg
Temperature resistance		-20 ° C
Temperature resistance to		60 ° C
tread and tyre hardness		80° Shore A
Bearing type		Ball bearing

