

EA986GG-75



EAN: 4047526274689

ID: 274688

Light duty fixed castor with top plate fitting, Wheel with solid rubber tyres, with synthetic rim


Bracket:

Made of pressed steel. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

Wheels:

Tyre & running tread: Made of high-quality solid rubber, very high operational comfort, low-noise operation, very good floor preservation. Tread colour: dark grey

Rim / wheel centre: Made of high-quality, impact-resistant nylon. Pressed-on tyre.



Technical data

Wheel Ø (D)	75 mm
Wheel width (T2)	25 mm
Load capacity	60 kg
Total height (H)	100 mm
Unit weight	0.282 kg
Temperature range from	-20 °C
Temperature range to	60 °C
Tread & tyre hardness	80° Shore A
Bearing type	
Plate size (A,B)	60 x 60 mm
Bolt hole Ø (d)	6,2 mm
Bolt hole spacing (a,b)	38x38/48x48 mm

Rolling resistance



Operating noise



Floor surface preservation



BPA-VPA 75K

Variants	
	Antistatic version
	With pressed steel thread guard, zinc-plated