

Product Data Sheet



B-VEHI 125R

EAN 4047526615055

ID 615054

**Heat-resistant pressed steel fixed castor with top plate fitting,
Heat-resistant Blickle TempLine® Basic wheel with solid rubber
tyres, with pressed steel rim**

Bracket:

Made of pressed steel. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

Wheels:

Made of heat-resistant solid rubber, high operational comfort, low-noise operation, good floor preservation, high tear resistance, PAH conform acc. to EU directive 2005/69/EC.

Tread/tyre: Made of heat-resistant solid rubber.

Tread colours black

Wheel centre/rim:

Pressed steel rim, zinc-plated, blue-passivated, Cr6-free.

Wheel centre colour: blue passivated



Rolling resistance

■ ■ □ □ □ Satisfactory

Operating noise

■ ■ ■ ■ □ Very good

**Floor surface
preservation**

■ ■ ■ ■ □ Very good

Product Data Sheet



Technical data

Plate size		100 x 85
Bolt hole spacing		80 x 60
Bolt hole Ø		9
Wheel Ø		125 mm (D)
Wheel width		37,5 mm (T2)
Load capacity		90 kg
Total height		150 mm (H)
unit weight		0,9 kg
Temperature resistance		-25 ° C
Temperature resistance to		200 ° C
tread and tyre hardness		80° Shore A
Bearing type:		Roller bearing

