

# Product Data Sheet



## B-VEHI 200R

**EAN** 4047526442675

**ID** 442673

**Heat-resistant pressed steel fixed castor with top plate fitting, Heat-resistant Blickle TempLine® Basic wheel with solid rubber tyres, with pressed steel rim**

**Bracket:**

Made of pressed steel. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

**Wheels:**

Made of heat-resistant solid rubber, high operational comfort, low-noise operation, good floor preservation, high tear resistance, PAH conform acc. to EU directive 2005/69/EC.

**Tread/tyre:** Made of heat-resistant solid rubber.

**Tread colours** black

**Wheel centre/rim:**

Pressed steel rim, zinc-plated, blue-passivated, Cr6-free.

**Wheel centre colour:** blue passivated



**Rolling resistance**

■ ■ □ □ □ Satisfactory

**Operating noise**

■ ■ ■ ■ □ Very good












**Floor surface preservation**

■ ■ ■ ■ □ Very good

# Product Data Sheet



## Technical data

Plate size		140 x 110
Bolt hole spacing		105 x 75-80
Bolt hole Ø		11
Wheel Ø		200 mm (D)
Wheel width		50 mm (T2)
Load capacity		180 kg
Total height		235 mm (H)
unit weight		2,4 kg
Temperature resistance		-25 ° C
Temperature resistance to		200 ° C
tread and tyre hardness		80° Shore A
Bearing type:		Roller bearing

