

EA986GQ-125



EAN: 4047526575311

ID: 575316

Light duty swivel castor with top plate fitting, Wheel with thermoplastic rubber tread, with polypropylene wheel centre


Bracket:

Made of pressed steel, with double ball bearing in the swivel head, ball protection by the special top plate and ball disc design. The special Blickle dynamic riveting process of the swivel head results in minimal swivel head play and smooth rolling characteristics with an increased service life achieved by the work hardening of the ball race grooves. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

Wheels:

Tyre & running tread: Made of high-quality thermoplastic rubber elastomer (TPE), high operational comfort, low-noise operation, low rolling and swivelling resistance, good floor preservation, chemically bonded for an inseparable connection to the wheel centre. Tread colour: grey

Rim / wheel centre: Made of high-quality, impact-resistant polypropylene. Chemically bonded.



Technical data

Wheel Ø (D)	125 mm
Wheel width (T2)	32 mm
Load capacity	120 kg
Total height (H)	161 mm
Offset swivel castor (F)	40 mm
Unit weight	0.759 kg
Temperature range from	-20 °C
Temperature range to	60 °C
Tread & tyre hardness	85° Shore A
Bearing type	
Plate size (A,B)	90 x 66 mm
Bolt hole Ø (d)	8,5 mm
Bolt hole spacing (a,b)	75x45/61x51 mm

Rolling resistance



Operating noise



Floor surface preservation



Blickle Räder+Rollen GmbH u. Co. KG

Heinrich-Blickle-Straße 1 · 72348 Rosenfeld · Germany

Telefon: +49 7428 932-0 · Telefax: +49 7428 932-209

E-Mail: info@blickle.com · Internet: www.blickle.com

© Blickle Räder+Rollen GmbH u. Co. KG 2013
Rosenfeld · Germany

LKPA-TPA 126K-FK

Variants



Electrically conductive
version, non-marking