

# Product Data Sheet



## LPA-TPA 75K-FK

EAN 4047526356392  
ID 356394

Light duty swivel castor with top plate fitting, Wheel with thermoplastic rubber tread, with polypropylene wheel centre

**Bracket:**

Made of pressed steel, with double ball bearing in the swivel head, strong central kingpin, ball protection by the special top plate and ball disc design. The special Blickle dynamic riveting process of the swivel head results in minimal swivel head play and smooth rolling characteristics with an increased service life achieved by the work hardening of the ball race grooves. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

**Wheels:**

Made of high-quality thermoplastic rubber elastomer (TPE), high operational comfort, low-noise operation, low rolling and swivelling resistance, good floor preservation, chemically bonded for an inseparable connection to the wheel centre.

**Tread/tyre:**

Made of thermoplastic rubber elastomer (TPE), contains traces of oil.

**Tread colours:** grey

**Wheel centre/rim:**

Made of high-quality, impact-resistant polypropylene. Chemically bonded.

**Wheel centre colour:** grey



**Rolling resistance**

Very good

**Operating noise**

Good

**Floor surface preservation**


Good

# Product Data Sheet



## Technical data

Plate size		60 x 60
Bolt hole spacing		38x38/48x48
Bolt hole Ø		6,2
Wheel Ø		75 mm (D)
Wheel width		25 mm (T2)
Load capacity		75 kg
Total height		100 mm (H)
Offset swivel castor		29 mm
unit weight		0,3 kg
Temperature resistance		-20 ° C
Temperature resistance to		60 ° C
tread and tyre hardness		85° Shore A
Bearing type:		Ball bearing



# Product Data Sheet



## Variants



### LPA-TPA 75K-FI-FK

Light duty swivel castor with top plate fitting with synthetic brake lever, Wheel with thermoplastic rubber tread, with polypropylene wheel centre



### LPA-TPA 75K-ELS-FK

Light duty swivel castor with top plate fitting, Wheel with thermoplastic rubber tread, with polypropylene wheel centre



### LPA-TPA 75K-FI-ELS-FK

Light duty swivel castor with top plate fitting with synthetic brake lever, Wheel with thermoplastic rubber tread, with polypropylene wheel centre