

# Product Data Sheet



## LE-VE 150R-FI

EAN 4047526532123

ID 532127

**Pressed steel swivel castor with top plate fitting and 'stop-fix' brake, Wheel with standard solid rubber tyres, with pressed steel rim**

### Bracket:

Made of pressed steel, with double ball bearing in the swivel head, ball protection by the special top plate and ball disc design. The special Blickle dynamic riveting process of the swivel head results in minimal swivel head play and smooth rolling characteristics with an increased service life achieved by the work hardening of the ball race grooves. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

### Wheels:

Made of standard solid rubber, very high operational comfort, low-noise operation, very good floor preservation, PAH conform acc. to EU directive 2005/69/EC.

**Tread/tyre:** Made of standard solid rubber.

**Tread colours** black

### Wheel centre/rim:

Pressed steel rim, zinc-plated, blue-passivated, Cr6-free.

**Wheel centre colour:** blue passivated



### Rolling resistance

■ ■ □ □ □ Satisfactory

### Operating noise

■ ■ ■ ■ □ Very good

### Floor surface preservation

■ ■ ■ ■ □ Very good

# Product Data Sheet



## Technical data

Plate size		140 x 110
Bolt hole spacing		105 x 75-80
Bolt hole Ø		11
Wheel Ø		150 mm (D)
Wheel width		40 mm (T2)
Load capacity		135 kg
Total height		190 mm (H)
Offset swivel castor		54 mm
unit weight		2,6 kg
Temperature resistance		-25 ° C
Temperature resistance to		80 ° C
tread and tyre hardness		80° Shore A
Bearing type:		Roller bearing

