

EA986HN-250



EAN: 4047526006372

ID: 6379

Pressed steel fixed castor, heavy duty brackets, with top plate fitting, Nylon wheel


Bracket:

Made of pressed steel. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

Wheels:

Tyre & running tread: Made of high-quality, impact-resistant nylon. Tread colour: natural white

Rim / wheel centre: -



Technical data

Wheel Ø (D)	250 mm
Wheel width (T2)	50 mm
Load capacity	900 kg
Total height (H)	295 mm
Unit weight	3.469 kg
Temperature range from	-25 °C
Temperature range to	80 °C
Tread & tyre hardness	70° Shore D
Bearing type	
Plate size (A,B)	140 x 110 mm
Bolt hole Ø (d)	11 mm
Bolt hole spacing (a,b)	105 x 75-80 mm

Rolling resistance



Operating noise



Floor surface preservation

