

Product Data Sheet



BK-PO 75R-FA

EAN 4047526362430

ID 362434

Pressed steel fixed castor, medium heavy duty brackets, with top plate fitting, Nylon wheel

Bracket:

Made of pressed steel. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

Wheels: Made of high-quality, impact-resistant nylon. **Tread colours:** natural white

Wheel centre/rim: - Wheel centre colour: natural white



Rolling resistance

■■■■■ Excellent

Operating noise

■■□□□ Satisfactory

Floor surface preservation

■■□□□ Satisfactory

Product Data Sheet



Technical data

Plate size		100 x 85
Bolt hole spacing		80 x 60
Bolt hole Ø		9
Wheel Ø		75 mm (D)
Wheel width		32 mm (T2)
Load capacity		200 kg
Total height		108 mm (H)
unit weight		0,5 kg
Temperature resistance		-25 ° C
Temperature resistance to		80 ° C
tread and tyre hardness		70° Shore D
Bearing type		Roller bearing

