

# Product Data Sheet



## LRA-VSTH 35K-GS10

EAN 4047526503017

ID 503011

**Light duty swivel castor with threaded pin, Heavy duty wheel with Blickle Extrathane® polyurethane tread, with steel wheel centre**

### Bracket:

Made of pressed steel, with double ball bearing in the swivel head, ball protection by the special top plate and ball disc design. The special Blickle dynamic riveting process of the swivel head results in minimal swivel head play and smooth rolling characteristics with an increased service life achieved by the work hardening of the ball race grooves. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

### Wheels:

Made of high-quality, reaction-injected polyurethane-elastomer Blickle Extrathane®, low-noise operation, low rolling resistance, good floor preservation, very high abrasion resistance, high cut and tear propagation resistance, very good chemical connection with the wheel centre.

### Tread/tyre:

Made of high-quality polyurethane-elastomer Blickle Extrathane®.

**Tread colours:** light brown

**Wheel centre/rim:** Made of steel. Casted tread.

**Wheel centre colour:** silver



### Rolling resistance

■■■■□ Very good

### Operating noise

■■■■□ Good

### Floor surface preservation

■■■■□ Good

# Product Data Sheet



## Technical data

Plate size		43
Bolt hole Ø		11
Wheel Ø		35 mm (D)
Wheel width		27 mm (T2)
Load capacity		80 kg
Total height		50 mm (H)
Offset swivel castor		15 mm
unit weight		0,2 kg
Temperature resistance		-25 ° C
Temperature resistance to		70 ° C
tread and tyre hardness		92° Shore A
Bearing type		Ball bearing

