

Product Data Sheet



LKRA-VSTH 50K-GS12

EAN 4047526125400

ID 845685

Light duty swivel castor with threaded pin, Heavy duty wheel with Blickle Extrathane® polyurethane tread, with steel wheel centre

Bracket:

Made of pressed steel, with double ball bearing in the swivel head, ball protection by the special top plate and ball disc design. The special Blickle dynamic riveting process of the swivel head results in minimal swivel head play and smooth rolling characteristics with an increased service life achieved by the work hardening of the ball race grooves. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

Wheels:

Made of high-quality, reaction-injected polyurethane-elastomer Blickle Extrathane®, low-noise operation, low rolling resistance, good floor preservation, very high abrasion resistance, high cut and tear propagation resistance, very good chemical connection with the wheel centre.

Tread/tyre:

Made of high-quality polyurethane-elastomer Blickle Extrathane®.

Tread colours: light brown

Wheel centre/rim: Made of steel. Casted tread.

Wheel centre colour: silver



Rolling resistance

■ ■ ■ ■ □ Very good

Operating noise

■ ■ ■ □ □ Good

Floor surface preservation

■ ■ ■ □ □ Good

Product Data Sheet



Technical data

Plate size		57
Bolt hole Ø		13
Wheel Ø		50 mm (D)
Wheel width		33 mm (T2)
Load capacity		150 kg
Total height		70 mm (H)
Offset swivel castor		29 mm
unit weight		0,5 kg
Temperature resistance		-25 ° C
Temperature resistance to		70 ° C
tread and tyre hardness		92° Shore A
Bearing type		Ball bearing

