

Product Data Sheet



B-VSTH 60K

EAN 4047526092382

ID 759412

Pressed steel compact fixed castor with top plate fitting, Heavy duty wheel with Blickle Extrathane® polyurethane tread, with steel wheel centre

Bracket:

Made of pressed steel. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

Wheels:

Made of high-quality, reaction-injected polyurethane-elastomer Blickle Extrathane®, low-noise operation, low rolling resistance, good floor preservation, very high abrasion resistance, high cut and tear propagation resistance, very good chemical connection with the wheel centre.

Tread/tyre:

Made of high-quality polyurethane-elastomer Blickle Extrathane®.

Tread colours: light brown

Wheel centre/rim: Made of steel. Casted tread.

Wheel centre colour: silver



Rolling resistance

■ ■ ■ ■ □ Very good

Operating noise

■ ■ ■ □ □ Good












Floor surface preservation

■ ■ ■ □ □ Good

Product Data Sheet



Technical data

Plate size		100 x 85
Bolt hole spacing		80 x 60
Bolt hole Ø		9
Wheel Ø		60 mm (D)
Wheel width		35 mm (T2)
Load capacity		200 kg
Total height		80 mm (H)
unit weight		0,6 kg
Temperature resistance		-25 ° C
Temperature resistance to		70 ° C
tread and tyre hardness		92° Shore A
Bearing type		Ball bearing

