

EA986HW-1



EAN: 4047526274719

ID: 274712

Light duty swivel castor with top plate fitting with synthetic brake lever, Nylon wheel

Bracket:

Made of pressed steel, with double ball bearing in the swivel head, ball protection by the special top plate and ball disc design. The special Blickle dynamic riveting process of the swivel head results in minimal swivel head play and smooth rolling characteristics with an increased service life achieved by the work hardening of the ball race grooves. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.


Wheels:

Tyre & running tread: Made of high-quality, impact-resistant nylon, very low rolling and swivelling resistance, smooth running performance on even floors, very high abrasion resistance. Tread colour: black

Rim / wheel centre: -

Variants:

mit Feststeller "stop-fix"



Technical data

Wheel Ø (D)	50 mm
Wheel width (T2)	18 mm
Load capacity	75 kg
Total height (H)	71 mm
Offset swivel castor (F)	25 mm
Unit weight	0.208 kg
Temperature range from	-25 °C
Temperature range to	80 °C
Tread & tyre hardness	70° Shore D
Bearing type	
Plate size (A,B)	60 x 60 mm
Bolt hole Ø (d)	6,2 mm
Bolt hole spacing (a,b)	38x38/48x48 mm

Rolling resistance



Operating noise



Floor surface preservation

