

B-POEV 100R

Pressed steel fixed castor, medium duty design, with top plate fitting, heavy duty wheel, with 'Blickle EasyRoll' elastic solid rubber tyres, with nylon wheel centre

EAN 4047526478988

ID 478982

Customs tariff number 87169090



Bracket: B series

- pressed steel, zinc-plated, blue-passivated, Cr6-free

Wheel: POEV series















- tyre: high-quality elastic solid rubber "Blickle EasyRoll" in smooth rolling quality, hardness 65 Shore A, colour black
- wheel centre: high-quality nylon 6, impact resistant, colour black

Other features:

- high chemical resistance to many aggressive substances, except oils
- operating temperature: -25 °C to +80 °C, temporarily up to +100 °C, reduced load capacity over +35 °C



Technical data:

Wheel Ø (D)		100 mm
Wheel width		32 mm
Load capacity at 4 km/h		200 kg
Load capacity (static)		500 kg
Bearing type		roller bearing
Total height (H)		125 mm
Plate size		100 x 85 mm
Bolt hole spacing		80 x 60 mm
Bolt hole Ø		9 mm
Temperature resistance min		-25 °C
Temperature resistance max		80 °C
Tread and tyre hardness		65 Shore A
Unit weight		0.595 kg
Non-marking		×
Electrically conductive		×
Antistatic		×
Corrosion-resistant		×
Heat-resistant		×
Non-staining		×
Tread hydrolysis-resistant		×
Suitable for autoclaves		×
Suitable for machine washing		×

Tread and tyre hardness

 65 Shore A

Rolling resistance

 very good

Wear resistance

 good

Operating noise / floor surface preservation

 very good

