

B-POEV 125R

Pressed steel fixed castor, medium duty design, with top plate fitting, heavy duty wheel, with 'Blickle EasyRoll' elastic solid rubber tyres, with nylon wheel centre

EAN 4047526410421

ID 410423

Customs tariff number 87169090



Bracket: B series

- pressed steel, zinc-plated, blue-passivated, Cr6-free

Wheel: POEV series

- tyre: high-quality elastic solid rubber "Blickle EasyRoll" in smooth rolling quality, hardness 65 Shore A, colour black
- wheel centre: high-quality nylon 6, impact resistant, colour black

Other features:

- high chemical resistance to many aggressive substances, except oils
- operating temperature: -25 °C to +80 °C, temporarily up to +100 °C, reduced load capacity over +35 °C



Technical data:

Wheel Ø (D)	125 mm
Wheel width	37 mm
Load capacity at 4 km/h	250 kg
Load capacity (static)	625 kg
Bearing type	roller bearing
Total height (H)	150 mm
Plate size	100 x 85 mm
Bolt hole spacing	80 x 60 mm
Bolt hole Ø	9 mm
Temperature resistance min	-25 °C
Temperature resistance max	80 °C
Tread and tyre hardness	65 Shore A
Unit weight	0.728 kg
Non-marking	×
Electrically conductive	×
Antistatic	×
Corrosion-resistant	×
Heat-resistant	×
Non-staining	×
Tread hydrolysis-resistant	×
Suitable for autoclaves	×
Suitable for machine washing	×

Tread and tyre hardness

65 Shore A

Rolling resistance

very good

Wear resistance

good

Operating noise / floor surface preservation

very good

