

LE-POEV 125R

Pressed steel swivel castor, with top plate fitting, heavy duty wheel, with 'Blickle EasyRoll' elastic solid rubber tyres, with nylon wheel centre

EAN 4047526320737

ID 320739

Customs tariff number 87169090



Bracket: LE series

- pressed steel, zinc-plated, blue-passivated, Cr6-free
- double ball bearing in the swivel head
- swivel head seal
- minimum swivel head play and smooth rolling characteristic and increased service life due to the special dynamic Blickle riveting process

Wheel: POEV series

- tyre: high-quality elastic solid rubber "Blickle EasyRoll" in smooth rolling quality, hardness 65 Shore A, colour black
- wheel centre: high-quality nylon 6, impact resistant, colour black

Other features:

- high chemical resistance to many aggressive substances, except oils
- operating temperature: -25 °C to +80 °C, temporarily up to +100 °C, reduced load capacity over +35 °C

Technical data:

Wheel Ø (D)	⌀	125 mm
Wheel width	⊥	37 mm
Load capacity at 4 km/h	⬇	150 kg
Load capacity (static)	⬇	375 kg
Bearing type	⊙	roller bearing
Total height (H)	⊘	150 mm
Plate size	⊞	100 x 85 mm
Bolt hole spacing	⊞	80 x 60 mm
Bolt hole Ø	⌀	9 mm
Offset (F)	⊘	38 mm
Temperature resistance min		-25 °C
Temperature resistance max		70 °C
Tread and tyre hardness		65 Shore A
Unit weight	⚖	0.786 kg
Non-marking	✗	
Electrically conductive	⊞	✗
Antistatic	⊞	✗
Corrosion-resistant		✗
Heat-resistant	⊞	✗
Non-staining		✗
Tread hydrolysis-resistant		✗
Suitable for autoclaves		✗
Suitable for machine washing		✗



Tread and tyre hardness

■■■■■ 65 Shore A

Rolling resistance

■■■■■ very good

Wear resistance

■■■■■ good

Operating noise / floor surface preservation

■■■■■ very good

