

## LE-POEV 125R-FI

Pressed steel swivel castor, with top plate fitting, with brake system 'stop-fix', heavy duty wheel, with 'Blickle EasyRoll' elastic solid rubber tyres, with nylon wheel centre

EAN 4047526410438

ID 410431

Customs tariff number 87169090



### Bracket: LE series

- pressed steel, zinc-plated, blue-passivated, Cr6-free
- double ball bearing in the swivel head
- swivel head seal
- minimum swivel head play and smooth rolling characteristic and increased service life due to the special dynamic Blickle riveting process

### Wheel: POEV series

- tyre: high-quality elastic solid rubber "Blickle EasyRoll" in smooth rolling quality, hardness 65 Shore A, colour black
- wheel centre: high-quality nylon 6, impact resistant, colour black

### Other features:

- high chemical resistance to many aggressive substances, except oils
- operating temperature: -25 °C to +80 °C, temporarily up to +100 °C, reduced load capacity over +35 °C

### Technical data:

Wheel Ø (D)	⌀	125 mm
Wheel width	⊥	37 mm
Load capacity at 4 km/h	⬆	150 kg
Load capacity (static)	⬆	375 kg
Bearing type	⊙	roller bearing
Total height (H)	⊘	150 mm
Plate size	⊞	100 x 85 mm
Bolt hole spacing	⊞	80 x 60 mm
Bolt hole Ø	⌀	9 mm
Offset (F)	⊞	40 mm
Temperature resistance min		-25 °C
Temperature resistance max		70 °C
Tread and tyre hardness		65 Shore A
Unit weight	⚖	0.917 kg
Non-marking	✗	
Electrically conductive	⚡	✗
Antistatic	⚡	✗
Corrosion-resistant	✗	
Heat-resistant	🔥	✗
Non-staining	✗	
Tread hydrolysis-resistant	✗	
Suitable for autoclaves	✗	
Suitable for machine washing	✗	



### Tread and tyre hardness

■■■■■ 65 Shore A

### Rolling resistance

■■■■■ very good

### Wear resistance

■■■■■ good

### Operating noise / floor surface preservation

■■■■■ very good

