

## Product data sheet

EAN 4047526562076

ID 562074

### LK-ALEV 100K-1



#### Rolling resistance

□□□□□ Very good

#### Operating noise

□□□□□ Very good

#### Floor surface preservation

□□□□□ Very good

**Pressed steel swivel castor, medium heavy duty brackets, with top plate fitting, Heavy duty wheel with elastic solid rubber tyres 'Blickle EasyRoll', with aluminium wheel centre**

#### Bracket:

Made of heavy pressed steel, swivel bracket with double ball bearing in the swivel head, swivel head seals. The special Blickle dynamic riveting process of the swivel head results in minimal swivel head play and smooth rolling characteristics with an increased service life achieved by the work hardening of the ball race grooves. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.

#### Wheels:

Made of high-quality elastic solid rubber, in smooth rolling quality "Blickle EasyRoll", very high operational comfort, low-noise operation, low rolling resistance, very good floor preservation, vulcanised on the wheel centre.

#### Tread/tyre:

Made of high-quality elastic solid rubber in smooth rolling quality "Blickle EasyRoll".













#### Wheel centre/rim:

Made of die-cast aluminium. Vulcanised tyre.

#### Wheel centre colour:

silver grey

## Technical data

<b>Plate size</b>		100 x 85
<b>Bolt hole spacing</b>		80 x 60
<b>Bolt hole Ø</b>		9
<b>Wheel Ø</b>		100 mm (D)
<b>Tyre width</b>		40 mm (T2)
<b>Load capacity</b>		200 kg
<b>Total height</b>		130 mm (H)
<b>Offset swivel castor</b>		45 mm
<b>Unit weight</b>		1,2 kg
<b>Temperature resistance</b>		-25 ° C
<b>Temperature range to</b>		80 ° C
<b>Belagshärte</b>		65° Shore A
<b>Bearing type</b>		Ball bearing

