Product Data Sheet



BH-GB 128K

EAN 4047526111977 **ID** 754046

Pressed steel fixed castor, heavy duty brackets, with top plate fitting, Heavy duty wheel with Blickle Besthane® polyurethane tread, with cast iron wheel centre

Bracket:

Made of pressed steel. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free.



Made of high-quality, reaction-injected polyurethane-elastomer Blickle Besthane®, low-noise operation, very low rolling resistance, high dynamic load capacity, good floor preservation, very high abrasion resistance, high cut and tear propagation resistance, very good chemical connection with the wheel centre.


Tread/tyre:

Made of high-quality polyurethane-elastomer Blickle Besthane®, high dynamic load capacity.

Tread colours brown

Wheel centre/rim: Made of steel. Casted tread.

Wheel centre colour: silver





Product Data Sheet



Technical data

| Plate size | | 140 x 110 |
|---------------------------|--------------|--------------|
| Bolt hole spacing | ¥ ¥ 4 | 105 x 75-80 |
| Bolt hole Ø | - | 11 |
| Wheel Ø | \odot | 125 mm (D) |
| Wheel width | , [], | 60 mm (T2) |
| Load capacity | 凸 | 700 kg |
| Total height | Q_ | 170 mm (H) |
| unit weight | Ø | 3,8 kg |
| Temperature resistance | B | -25 ° C |
| Temperature resistance to | | 70 ° C |
| tread and tyre hardness | | 92° Shore A |
| Bearing type: | • | Ball bearing |

