

EA986KS-300



EAN: 4047526294946

ID: 294942

Welded steel heavy duty twin wheel fixed castor, Heavy duty wheel with Blickle Extrathane® polyurethane tread, with cast iron wheel centre


Bracket:

Particularly rugged welded steel construction. Bolted wheel axle. Zinc-plated, yellow-passivated, Cr6-free.

Wheels:

Tyre & running tread: Made of high-quality, reaction-injected polyurethane-elastomer Blickle Extrathane®, low-noise operation, low rolling resistance, good floor preservation, very high abrasion resistance, high cut and tear propagation resistance, very good chemical connection with the wheel centre. Tread colour: light brown

Rim / wheel centre: Made of grey cast iron, with grease nipple, lacquered.



Technical data

Wheel Ø (D)	300 mm
Wheel width (T2)	2 x 80 mm
Load capacity	4300 kg
Total height (H)	390 mm
Unit weight	41.6 kg
Temperature range from	-25 °C
Temperature range to	70 °C
Tread & tyre hardness	92° Shore A
Bearing type	
Plate size (A,B)	200 x 255 mm
Bolt hole Ø (d)	18 mm
Bolt hole spacing (a,b)	160 x 210 mm

Rolling resistance



Operating noise



Floor surface preservation

