## **Product Data Sheet**



## **BSD-GSPO 80K**

**EAN** 4047526614621 **ID** 614628

Welded steel heavy duty twin wheel fixed castor, Heavy duty wheels made of cast nylon

#### **Bracket:**

Particularly rugged welded steel construction. Bolted wheel axle. Zir plated, yellow-passivated, Cr6-free.



Made of high-quality, impact-resistant nylon, very rugged, heavy wheel design, very low rolling and swivelling resistance, smooth running performance on even floors, very high abrasion resistance.


#### Tread/tyre:

Made of high-quality, impact-resistant cast nylon.

Tread colours natural beige

Wheel centre/rim: -

Wheel centre colour: natural beige





## Operating noise

■ □ □ □ Satisfactory

# Floor surface preservation

■■□□□ Satisfactory

# **Product Data Sheet**



### **Technical data**

Plate size		110 x 140
Bolt hole spacing		75-80 x 105
Bolt hole Ø	4	11
Wheel Ø	$\odot$	80 mm (D)
Wheel width	<b>,</b> □,	2 x 40 mm (T2)
Load capacity	ටී	1750 kg
Total height	<u> Z</u>	125 mm (H)
unit weight	<b>B</b>	2,6 kg
Temperature resistance	<b>ا</b>	-25 ° C
Temperature resistance to	<u>ا</u>	80 ° C
tread and tyre hardness		80° Shore D
Bearing type:	•	Ball bearing

