

EA986KX-300



EAN: 4047526334529

ID: 334524

Welded steel heavy duty fixed castor, Heavy duty wheels made of cast nylon

Bracket:

Particularly rugged welded steel construction. Bolted wheel axle. Zinc-plated, yellow-passivated, Cr6-free.

Wheels:

Tyre & running tread: Made of high-quality, impact-resistant, hard and tough, highly compressed cast nylon with outstanding load capacity, very low rolling and swivelling resistance, smooth running performance on even floors, very high abrasion resistance. Tread colour: natural beige

Rim / wheel centre: -



Technical data

Wheel Ø (D)	300 mm
Wheel width (T2)	110 mm
Load capacity	10000 kg
Total height (H)	430 mm
Unit weight	56.884 kg
Temperature range from	-25 °C
Temperature range to	80 °C
Tread & tyre hardness	80° Shore D
Bearing type	
Plate size (A,B)	400 x 300 mm
Bolt hole Ø (d)	26 mm
Bolt hole spacing (a,b)	340 x 240 mm

Rolling resistance



Operating noise



Floor surface preservation

