

EA986KY-400



EAN: 4047526301644

ID: 301648

Welded steel heavy duty swivel castor, strong swivel head design, Heavy duty wheels made of cast nylon


Bracket:

Particularly rugged welded steel construction, with axial grooved ball bearing DIN 711 and tapered roller bearing DIN 720 in the swivel head, dust and splash-proof, fitted grease nipple, bolted and secured with a welded very strong central kingpin. Bolted wheel axle. Lacquered, red.

Wheels:

Tyre & running tread: Made of high-quality, impact-resistant, hard and tough, highly compressed cast nylon with outstanding load capacity, very low rolling and swivelling resistance, smooth running performance on even floors, very high abrasion resistance. Tread colour: natural beige

Rim / wheel centre: -




Technical data

Wheel Ø (D)	400 mm
Wheel width (T2)	110 mm
Load capacity	12000 kg
Total height (H)	530 mm
Offset swvl castor (F)	125 mm
Unit weight	84.3 kg
Temperature range from	-25 °C
Temperature range to	80 °C
Tread & tyre hardness	80° Shore D
Bearing type	
Plate size (A,B)	400 x 300 mm
Bolt hole Ø (d)	26 mm
Bolt hole spacing (a,b)	340 x 240 mm

Rolling resistance



Operating noise



Floor surface preservation

