

# Product Data Sheet



## BX-POTH 125G

EAN 4047526503376

ID 503375

**Stainless steel fixed castor, medium duty brackets, with top plate fitting, Wheel with thermoplastic polyurethane tread, with heavy nylon wheel centre, non-marking, non-staining**

### Bracket:

Made of pressed high-quality, chromium-nickel stainless steel (Material No. 1.4301/AISI 304). All parts incl. axle material are corrosion-resistant. Bolted wheel axle. Vibration-ground finished.

### Wheels:

Made of high-quality thermoplastic polyurethane, high operational comfort, low-noise operation, low rolling and swivelling resistance, good floor preservation, very high abrasion resistance, chemically bonded for an inseparable connection to the wheel centre.

**Tread colours:** dark grey

**Wheel centre/rim:** Made of high-quality, impact-resistant nylon.

**Wheel centre colour:** natural white

**Variant:** non-marking, non-staining



### Rolling resistance

■■■■□ Very good

### Operating noise

■■■■□□ Good

### Floor surface preservation

■■■■□□ Good

### Technical data

|   |  |             |
|---|--|-------------|
| Plate size  |  | 100 x 85    |
| Bolt hole spacing                                 |  | 80 x 60     |
| Bolt hole Ø                                       |  | 9           |
| Wheel Ø   |  | 125 mm (D)  |
| Wheel width                                       |  | 40 mm (T2)  |
| Load capacity                                     |  | 250 kg      |
| Total height                                      |  | 150 mm (H)  |
| unit weight                                       |  | 0,7 kg      |
| Temperature resistance                            |  | -25 ° C     |
| Temperature resistance to tread and tyre hardness |  | 70 ° C      |
| tread and tyre hardness                           |  | 94° Shore A |
| Bearing type                                      |  | Plain bore  |

