

EA986MD-3




EAN: 4047526006891

ID: 6890

Heavy duty nylon wheel

Tyre & running tread: Made of high-quality, impact-resistant nylon, very rugged, heavy wheel design, very low rolling and swivelling resistance, smooth running performance on even floors, very high abrasion resistance.
Tread colour: natural white

Rim / wheel centre: -



Technical data

Wheel Ø (D)	75 mm
Wheel width (T2)	32 mm
Load capacity	300 kg
Axle bore Ø (d)	15 mm
Hub length (T1)	35 mm
Unit weight	0.192 kg
Temperature range from	-25 °C
Temperature range to	80 °C
Tread & tyre hardness	70° Shore D
Bearing type	

Rolling resistance



Operating noise



Floor surface preservation



Blickle Räder+Rollen GmbH u. Co. KG

Heinrich-Blickle-Straße 1 · 72348 Rosenfeld · Germany

Telefon: +49 7428 932-0 · Telefax: +49 7428 932-209

E-Mail: info@blickle.com · Internet: www.blickle.com

© Blickle Räder+Rollen GmbH u. Co. KG 2013
Rosenfeld · Germany