

POTH 100/15G

EAN 4047526044374
ID 44370

Wheel with thermoplastic polyurethane tread, with heavy nylon wheel centre, non-marking, non-staining

Wheels:

Made of high-quality thermoplastic polyurethane, high operational comfort, low-noise operation, low rolling and swivelling resistance, good floor preservation, very high abrasion resistance, chemically bonded for an inseparable connection to the wheel centre.

Tread/tyre:

Made of high-quality thermoplastic polyurethane.

Tread colours: dark grey

Wheel centre/rim:

Made of high-quality, impact-resistant nylon.

Wheel centre colour: natural white

Variant: non-marking, non-staining












- Rolling resistance

Very good
- Operating noise

Good
- Floor surface preservation

Good

Technical data

Wheel Ø		100 mm (D)
Wheel width		35 mm (T2)
Load capacity		300 kg
Axle bore Ø		15 mm (d)
Hub length		45 mm (T1)
unit weight		0,2 kg
Temperature resistance		-25 ° C
Temperature resistance to tread and tyre hardness		70 ° C
Bearing type:		Plain bore

