

Product Data Sheet



POTH 150/20G

EAN 4047526044411

ID 44412

Wheel with thermoplastic polyurethane tread, with heavy nylon wheel centre, non-marking, non-staining

Wheels:

Made of high-quality thermoplastic polyurethane, high operational comfort, low-noise operation, low rolling and swivelling resistance, good floor preservation, very high abrasion resistance, chemically bonded for an inseparable connection to the wheel centre.

Tread/tyre:

Made of high-quality thermoplastic polyurethane.

Tread colours: dark grey

Wheel centre/rim:

Made of high-quality, impact-resistant nylon.

Wheel centre colour: natural white

Variant: non-marking, non-staining



Rolling resistance

■■■■□ Very good

Operating noise

■■■■□□ Good

Floor surface preservation

■■■■□□ Good

Technical data

Wheel Ø	⊘	150 mm (D)
Wheel width	∟	45 mm (T2)
Load capacity	⊞	500 kg
Axle bore Ø	⊘	20 mm (d)
Hub length	∟	60 mm (T1)
unit weight	⊞	0,5 kg
Temperature resistance	🔥	-25 ° C
Temperature resistance to tread and tyre hardness	🔥	70 ° C
Bearing type:	⊙	Plain bore

