

# Product Data Sheet



## POTH 75/15G

EAN 4047526251482

ID 251488

**Wheel with thermoplastic polyurethane tread, with heavy nylon wheel centre, non-marking, non-staining**

### Wheels:

Made of high-quality thermoplastic polyurethane, high operational comfort, low-noise operation, low rolling and swivelling resistance, good floor preservation, very high abrasion resistance, chemically bonded for an inseparable connection to the wheel centre.

### Tread/tyre:

Made of high-quality thermoplastic polyurethane.

**Tread colours:** dark grey

### Wheel centre/rim:

Made of high-quality, impact-resistant nylon.

**Wheel centre colour:** natural white

**Variant:** non-marking, non-staining



### Rolling resistance

■■■■□ Very good

### Operating noise

■■■■□□ Good

### Floor surface preservation

■■■■□□ Good

### Technical data

Wheel Ø	⊘	75 mm (D)
Wheel width	⊥	37 mm (T2)
Load capacity	⊞	200 kg
Axle bore Ø	⊘	15 mm (d)
Hub length	⊥	45 mm (T1)
unit weight	⊞	0,2 kg
Temperature resistance	🔥	-25 ° C
Temperature resistance to tread and tyre hardness	🔥	70 ° C
Bearing type:	⊙	Plain bore

