

# Product Data Sheet



## V 302/25-75R

EAN 4047526584504

ID 584508

### Wheel with standard solid rubber tyres, with pressed steel rim

#### Wheels:

Made of standard solid rubber, very high operational comfort, low-noise operation, very good floor preservation, PAH conform acc. to EU directive 2005/69/EC.

**Tread colours:** black

#### Wheel centre/rim:

Pressed steel rim with tubular steel hub, bolted, zinc-plated, blue-passivated, Cr6-free.

**Wheel centre colour:** blue passivated



#### Rolling resistance

■ ■ ■ ■ Satisfactory

#### Operating noise

■ ■ ■ ■ Very good

#### Floor surface preservation

■ ■ ■ ■ Very good

### Technical data

Wheel Ø		300 mm (D)
Tyre width		60 mm (T2)
Load capacity		300 kg
Axle bore Ø		25 mm (d)
Hub length		75 mm (T1)
unit weight		4,3 kg
Temperature resistance		-25 ° C
Temperature resistance to		80 ° C
tread and tyre hardness		80° Shore A
Bearing type		Roller bearing

