

Product Data Sheet



PHN 125/15IK

EAN 4047526583538

ID 583534

Heat-resistant Blickle TempLine® Classic thermoset wheel

Wheels:

Made of phenolic resin, very high static load capacity, smooth running performance on even floors.

Tread colours: black

Wheel centre/rim: - Wheel centre colour: black



Rolling resistance

■■■■■ Excellent

Operating noise

■■■■□ Satisfactory

Floor surface preservation

■■■■□ Satisfactory

Technical data

Wheel Ø		125 mm (D)
Wheel width		40 mm (T2)
Load capacity		200 kg
Axle bore Ø		15 mm (d)
Hub length		40 mm (T1)
unit weight		0,8 kg
Temperature resistance		-35 ° C
Temperature resistance to		260 ° C
tread and tyre hardness		90° Shore D
Bearing type		Ball bearing

