

Product Data Sheet



BS-SPK 200K

EAN 4047526076283

ID 76281

Welded steel heavy duty fixed castor, Cast iron flanged wheel

Bracket:

Particularly rugged welded steel construction with reinforced fork for an improved absorption of axial forces. Bolted wheel axle. Zinc-plated, yellow-passivated, Cr6-free.

Wheels:

Made of rugged grey cast iron, with grease nipple, machined tread with horizontal taper of 3°, exceptionally low rolling resistance, outstanding wear resistance, lacquered.

Tread colours: silver

Wheel centre/rim: - Wheel centre colour: silver



Rolling resistance

■■■■■ Excellent

Operating noise

■□□□□ Sufficient

Floor surface preservation

■□□□□ Sufficient

Product Data Sheet



Technical data

Plate size		140 x 110
Bolt hole spacing		105 x 75-80
Bolt hole Ø		11
Wheel Ø without flange		mm (D)
Wheel Ø without flange		200 mm (D)
Tread width without flange		mm (T3)
Tread width		38 mm (T3)
Flange length		10 mm (T4)
Load capacity		1500 kg
Axle bore Ø		11 mm (d)
Total height		245 mm (H)
unit weight		9,6 kg
Temperature resistance		-25 ° C
Temperature resistance to		120 ° C
tread and tyre hardness		180 - 220 HB
Bearing type		Ball bearing

