

Product Data Sheet



DSPK 101K

EAN 4047526268350

ID 268359

Solid steel double flanged wheel

Wheels:

Made of mild steel, with lightly oiled surface, V-shaped tread (for angular steel), extremely low rolling resistance, extremely wear-resistant, particularly high static and dynamic load capacity.

Tread colours: silver

Wheel centre/rim: -



Rolling resistance

■■■■■ Excellent

Operating noise

■□□□□ Sufficient

Floor surface preservation

■□□□□ Sufficient

Technical data

Wheel Ø		100 mm (D)
Wheel width		40 mm (T2)
Recess width		20 mm (B)
Load capacity		600 kg
Axle bore Ø		15 mm (d)
Hub length		40 mm (T1)
unit weight		2 kg
Temperature resistance		-25 ° C
Temperature resistance to		120 ° C
tread and tyre hardness		190 - 230 HB
Bearing type		Ball bearing

