

Product Data Sheet



SVS 127/30K

EAN 4047526584917

ID 584912

Extra heavy duty solid steel wheel

Wheels:

Made of mild steel, with slightly crowned tread and lightly oiled surface, very low rolling and swivelling resistance, smooth running performance on even floors, extremely wear-resistant, particularly high static and dynamic load capacity.

Tread colours: silver

Wheel centre/rim: - Wheel centre colour: silver



Rolling resistance

■■■■■ Excellent

Operating noise

■□□□□ Sufficient

Floor surface preservation

■□□□□ Sufficient

Technical data

Wheel Ø		125 mm (D)
Wheel width		55 mm (T2)
Load capacity		2750 kg
Axle bore Ø		30 mm (d)
Hub length		60 mm (T1)
unit weight		4,4 kg
Temperature resistance		-25 ° C
Temperature resistance to		120 ° C
tread and tyre hardness		190 - 230 HB
Bearing type		Ball bearing

