

# EA986SG-100




**EAN: 4047526367084**

**ID: 367086**

**Cast nylon flanged wheel**

**Tyre & running tread:** Made of mild steel, with lightly oiled surface, V-shaped tread (for angular steel), extremely low rolling resistance, extremely wear-resistant, particularly high static and dynamic load capacity. Tread colour: natural beige  
**Rim / wheel centre:** -



### Technical data

Wheel Ø (D)	100 mm
Wheel Ø incl. flange (D1)	125 mm
Wheel width (T2)	46 mm
Tread width without flange (T3)	36 mm
Flange length (T4)	13 mm
Load capacity	600 kg
Axle bore Ø (d)	20 mm
Hub length (T1)	52 mm
Unit weight	0.628 kg
Temperature range from	-25 °C
Temperature range to	80 °C
Tread & tyre hardness	80° Shore D
Bearing type	

Rolling resistance



Operating noise



Floor surface preservation

