



Artikel-Nr.	Gewinde	WLL [t]	L [mm]	B [mm]	C [mm]	A [mm]	D1 [mm]	Gewicht [kg/100 Stk]
32300100	EA987GK-11 M10	0,45	18	13	46	30	38	52,00
32300120	EA987GK-12 M12	0,50	18	13	46	30	38	52,00
32300160	EA987GK-13 M16	1,12	20	13	46	30	38	54,00
32300200	EA987GK-14 M20	2,00	30	16	57	35	50	108,00
32300240	EA987GK-15 M24	3,15	30	18	70	40	58	162,00
32300300	EA987GK-16 M30	5,30	38	22	65	50	75	318,00
32300301	EA987GK-17 M30	8,00	38	22	95	50	80	361,00
32300360	EA987GK-18 M36	8,00	50	22	95	50	80	373,00
32300361	EA987GK-19 M36	10,00	50	25	90	50	85	453,00