

High pressure hose-G 1/8" male

11 x 500 mm

Item number: 12 765
EAN: 4103810127656
Discount group: A



Technical data

Connection on both ends:	G 1/8" male
Burst pressure (bar):	900
Outside diameter (mm):	11
Wrench size (SW) (mm):	15
Design:	acc. to DIN 1283
Materials	
Casing:	polyurethane, microbe-stabilized
Inner hose:	polyamide 6, soft
Reinforcement:	polyester, high-strength
Length (mm):	500
Weight (kg):	0,085

Packaging

Packing unit: 1,0