



Grease gun filling system-manually operated

20-kg-BE-Ø 270-310 mm

Item number: 17 820
EAN: 4103810178207
Discount group: A

Technical data

Pumping media:	lubricating greases, up to NLGI 2
Delivery rate/stroke (cm ³):	30
Grease supply:	by means of a hand pump
Follower plate:	for 20 kg container
Ø follower plate (mm):	270 – 310
Length of suction tube (mm):	510 mm
Connection suction side:	for grease guns, with filling nipple
Discharge pressure up to (bar):	8
Material pump body:	steel
Material pump head:	impact-resistant zinc die casting
Surface treatment:	all steel components are galvanized
Lacquering dust cover:	blue, Pantone 294 C
Application:	for filling lever, one hand and air operated grease guns

Specification

- Pump
- Suction tube
- Filling nipple, M 10 x 1 (12 670), enclosed without package, for upgrading grease guns from other manufacturers
- Dust cover (17 176), stabilising-fixing bracket (17 197) and follower plate (17 300)
- Dust cap on filling coupler secured by chain
- Packed in single carton box

Special notes

- for filling lever, one hand and air operated grease guns

Packaging

Dimensions packaging LxWxH (mm): 670 x 420 x 100
Weight including package (kg): 4,92
Packing unit: 1.0