



Abschmiersystem-handbetrieben

20 kg-BE -Ø 270-310 mm-SRL 510

Item number: 17 620
EAN: 4103810176203
Discount group: A

Technical data

Pumping media: lubricating greases, up to NLGI 2
 Delivery rate to refill grease gun / stroke (cm³): 30
 Length of discharge hose (mm): 1500
 Grease supply into the hand operated grease gun: manually lever operated
 Follower plate: for 20 kg container
 Ø follower plate (mm): 270 – 310
 Length of suction tube (mm): 510
 Connection hose/one hand grease gun: quick release adapter Rectus, type 26 (17 601), with non-return valve
 Delivery rate EHFP / stroke (cm³): 0,4
 Discharge pressure up to (bar): 550
 Burst pressure EHFP (bar): 850
 Burst pressure grease gun head (bar): 1200
 Capacity EHFP (cm³): 125
 Grease gun connection, pressure-side: M 10 x 1
 Grease pump piston actuation: manual, by means of pressure grip
 Material pump body: steel - NFA 35-561
 Material pump head: impact-resistant zinc die casting
 Surface treatment: all steel components are galvanized
 Lacquering dust cover: blue, Pantone 294 C

Specification

- Manual pump to refill one hand operated grease gun
- Pump
- Suction tube
- Dust cover (17 176), stabilising-fixing bracket (17 197) and follower plate (17 300)
- One hand operated grease gun (EHFP), connection M 10 x 1 (17 600)
- Spout, straight, M 10 x 1, 150 mm (12 435)
- Coupler, 4 jaws, M 10 x 1 (12 631)
- Discharge hose (17 003)
- Packed in single carton box

Packaging

Dimensions packaging LxWxH (mm): 670 x 420 x 100
 Weight including package (kg): 6
 Packing unit: 1,0