


A型 規格頭 (Gネジ)

単位 mm



規格	EA品番	呼びD	寸 法		
			H	S	B × C
GNA10M10K	EA991CZ-10A	M10 × 1.0	20	9	10
GNA3K	EA991CZ-13G	G3/8	24.5	10.5	17
GNA2-28K	EA991CZ-42F	1/4 × 28山	13.5	5	7