

655 EISENHOWER DRIVE OWATONNA, MN 55060 USA PHONE: (507) 455-7000 TECH. SERV.: (800) 533-6127 FAX: (800) 955-8329

ORDER ENTRY: (800) 533-6127 FAX: (800) 283-8665

INTERNATIONAL SALES: (507) 455-7223

FAX: (507) 455-7063


Form No. 542659

Parts List &


Operating Instructions for: 1577

Transfer Tanker

Max. Capacity: 30 liters (8 gallons)



PARTS LIST



Issue Date: Rev. B March 5, 2015

SAFETY PRECAUTIONS





CAUTION: To prevent personal injury,






 Lift with your legs keeping your back straight, and avoid twisting by moving your feet and not your waist. Get help when lifting heavy loads.

OPERATING INSTRUCTIONS

- 1. Lift the splash screen off the tank to expose the fluid inlet plug.
- 2. Remove the fluid inlet plug, and place it on the tank storage spot for safekeeping.
- 3. Replace the splash screen over the open fluid inlet hole.
- 4. Roll the tanker into position, and release the fluid into the tanker.
- 5. When finished, replace the fluid inlet plug, and roll the tanker to a waste fluid collection area.
- 6. Open the vent plug.
- 7. Have someone help when lifting the transfer tanker to empty its contents.
- 8. Open the drain plug to pour out the waste fluid.
- 9. Dispose of waste fluids according to local, state, and federal laws.





Refer to any operating instructions included with the product for detailed information about operation, testing, disassembly, reassembly, and preventive maintenance.

Items found in this list have been carefully tested and selected. Therefore: Use only genuine replacement parts! Additional questions can be directed to our Technical Service Department.