

Hydraulische Wagenheber *Hydraulic Bottle Jacks*

AX 100-300



- Große Hubhöhe
high lifting height
- Lange Einstellspindel
adjustable extension spindle



A 2-170 EA993BC-2 A 5-212 EA993BC-5 A 10-220 EA993BC-10 A 12-230 A 8-220 A 3.5-170 EA993BC-3.5

品番

品番	Belastung/ Capacity	Typ/Type	Best-Nr./ ID-No.	A mm	B mm	C mm	D mm	E mm	F mm	kg
EA993BC-2	2.000 kg	A 2-170	250.180.5	170	92	115	377	28	103x105	2,9
EA993BC-3.5	3.500 kg	A 3.5-170	027.727.4	170	92	115	377	28	103x105	2,9
EA993BC-5	5.000 kg	A 5.212	027.730.4	212	100	150	462	40	110x110	3,9
	8.000 kg	AX 8-220	250.039.6	220	110	150	480	48	124x122	5,7
EA993BC-10	10.000 kg	A 10-220	210.731.7	220	110	150	480	48	124x122	5,7
	12.000 kg	A 12-230	250.012.4	230	110	157	497	48	134x120	7,1
EA993BB-15	15.000 kg	AX 15-230	250.394.8	230	110	155	495	60	139,5x130	8,3
EA993BC-20	20.000 kg	AX 20-240	150.037.6	240	110	155	505	60	164x160	10,7
	25.000 kg	AH 25-240	150.015.5	240	118	157	515	65	185x176	13,1
EA993BC-30	30.000 kg	A 30-240	150.007.4	240	100	142	482	65	185x176	14,5
EA993BC-50	50.000 kg	A 50-250	150.041.4	250	-	155	405	72	290x235	33,0
	100.000 kg	AX 100-300	803.633.0	300	-	150	450	95	330x295	87,0

Abbildungen unverbindlich
Techn. Änderungen vorbehalten



AX 20-240 A 30-240 AH 25-240 AX 15-230

