


| 呼び径 D | 外径公差 | 長さ公差 (b、L、ℓ) |
|--------------|-----------|--------------|
| φ 75～φ 700 | -1.2～-1.9 | 0～+1 |
| φ 750～φ 1000 | -2.0～-2.2 | 0～+1 |

平成22年度版/公共建築工事標準仕様書に準じています。



$$L = D3 + 100$$

$$L1 = 0.5 \times D3 + 50$$

$$L2 = 0.5 \times D3 + 50$$

$$L3 = 0.5 \times D1 + 50$$

単位：mm

| 呼び径 | 板厚 | b1 | b3 | L | L3 | a | c | |
|-----|-----|-----|----|----|-----|-----|----|----|
| D1 | D3 | t | b2 | b3 | L | L3 | a | c |
| 75 | 75 | 0.6 | 8 | 8 | 175 | 90 | 60 | 60 |
| 100 | 75 | 0.6 | 8 | 8 | 175 | 100 | 60 | 60 |
| | 100 | 0.6 | 8 | 8 | 200 | 100 | 60 | 60 |
| 125 | 75 | 0.6 | 8 | 8 | 175 | 115 | 60 | 60 |
| | 100 | 0.6 | 8 | 8 | 200 | 115 | 60 | 60 |
| 150 | 75 | 0.6 | 10 | 8 | 175 | 125 | 60 | 60 |
| | 100 | 0.6 | 10 | 8 | 200 | 125 | 60 | 60 |
| 175 | 75 | 0.6 | 10 | 8 | 175 | 140 | 60 | 60 |
| | 100 | 0.6 | 10 | 8 | 200 | 140 | 60 | 60 |
| 200 | 75 | 0.6 | 10 | 10 | 250 | 140 | 60 | 60 |
| | 100 | 0.6 | 10 | 10 | 250 | 140 | 60 | 60 |
| 225 | 75 | 0.6 | 10 | 10 | 250 | 150 | 60 | 60 |
| | 100 | 0.6 | 10 | 10 | 250 | 150 | 60 | 60 |
| 250 | 75 | 0.6 | 10 | 10 | 275 | 150 | 60 | 60 |
| | 100 | 0.6 | 10 | 10 | 275 | 150 | 60 | 60 |
| 275 | 75 | 0.6 | 10 | 10 | 300 | 150 | 60 | 60 |
| | 100 | 0.6 | 10 | 10 | 300 | 150 | 60 | 60 |

| 呼び径 | 板厚 | b1 | b3 | L | L3 | a | c | |
|-----|-----|-----|----|----|-----|-----|----|----|
| D1 | D3 | t | b2 | b3 | L | L3 | a | c |
| 225 | 100 | 0.6 | 10 | 8 | 200 | 165 | 60 | 60 |
| | 125 | 0.6 | 10 | 8 | 225 | 165 | 60 | 60 |
| | 150 | 0.6 | 10 | 10 | 250 | 165 | 60 | 60 |
| | 175 | 0.6 | 10 | 10 | 275 | 165 | 60 | 60 |
| | 200 | 0.6 | 10 | 10 | 300 | 165 | 60 | 60 |
| 250 | 100 | 0.6 | 10 | 10 | 250 | 175 | 60 | 60 |
| | 125 | 0.6 | 10 | 8 | 225 | 175 | 60 | 60 |
| | 150 | 0.6 | 10 | 10 | 250 | 175 | 60 | 60 |
| | 175 | 0.6 | 10 | 10 | 275 | 175 | 60 | 60 |
| | 200 | 0.6 | 10 | 10 | 300 | 175 | 60 | 60 |
| 275 | 100 | 0.6 | 10 | 10 | 325 | 175 | 60 | 60 |
| | 125 | 0.6 | 10 | 10 | 350 | 175 | 60 | 60 |
| | 150 | 0.6 | 10 | 8 | 250 | 190 | 60 | 60 |
| | 175 | 0.6 | 10 | 10 | 275 | 190 | 60 | 60 |
| | 200 | 0.6 | 10 | 10 | 300 | 190 | 60 | 60 |
| 275 | 225 | 0.6 | 10 | 10 | 325 | 190 | 60 | 60 |
| | 250 | 0.6 | 10 | 10 | 350 | 190 | 60 | 60 |

| 呼び径 | 板厚 | b1 | b3 | L | L3 | a | c | |
|-----|-----|-----|----|----|-----|-----|----|----|
| D1 | D3 | t | b2 | b3 | L | L3 | a | c |
| 275 | 275 | 0.6 | 10 | 10 | 375 | 190 | 60 | 60 |
| | 100 | 0.6 | 10 | 8 | 200 | 200 | 60 | 60 |
| | 125 | 0.6 | 10 | 8 | 225 | 200 | 60 | 60 |
| | 150 | 0.6 | 10 | 10 | 250 | 200 | 60 | 60 |
| | 175 | 0.6 | 10 | 10 | 275 | 200 | 60 | 60 |
| 300 | 200 | 0.6 | 10 | 10 | 300 | 200 | 60 | 60 |
| | 225 | 0.6 | 10 | 10 | 325 | 200 | 60 | 60 |
| | 250 | 0.6 | 10 | 10 | 350 | 200 | 60 | 60 |
| | 275 | 0.6 | 10 | 10 | 375 | 200 | 60 | 60 |
| | 300 | 0.6 | 10 | 10 | 400 | 200 | 60 | 60 |

※材質：亜鉛鋼板

| | | | | | |
|----|----------------|---------|------|----|------------|
| 名称 | T管 | | | | |
| 型式 | T (φ 75～φ 300) | | | | |
| 承認 | 検図 | 製図 | 尺度 | 図番 | 08-211007 |
| | 橋本 | 工藤 | FREE | 図法 | 三角法 |
| | | | | 日附 | 2008.11.28 |
| 記号 | 2011.4.1 | 仕様書年度変更 | | | |
| 備考 | | | | | |

株式会社 深川製作所